



SS Stainless Steel

1 Type

- SC** With key (Keyed alike)
- SCKN** With wing knob (Keyed alike)
- SCTN** With T-handle (Keyed alike)

Metric table



Dimensions in: millimeters - inches

Latch arm distance A															d		h	
6	10	14	18	20	22	24	26	28	30	34	38	40	50	Type SC	Type SCKN, SCTN	Type SC	Type SCKN, SCTN	
6	10	14	18	20	22	24	26	28	30	34	38	40	50	28	32	4	6	
0.24	0.39	0.55	0.71	0.79	0.87	0.94	1.02	1.10	1.18	1.34	1.50	1.57	1.97	1.10	1.26	0.16	0.24	

Specification



- Cam lock housing
Stainless steel
- Type SC
Stainless steel AISI 303
- Type SCKN, SCTN
Stainless steel AISI 316
- Latch arm
Stainless steel AISI 304
- Key
Nickel silver with plastic hand piece
- Operating elements (Type SCKN, SCTN)
Stainless steel AISI 316
- Other parts
 - Type SC
Stainless steel AISI 304
 - Type SCKN, SCTN
Stainless steel AISI 316
- Protection class IP 65
- IP Protection Classes → page QVX
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 115 cam locks lock by a turning operation limited to 90° which moves the lock-in behind the door frame. The bevels of the locking ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.

The cam locks are delivered with 2 keys and loosely enclosed latch arm. The key can be removed in both end positions. The lock is standard, so that every lock can be opened with the same key.

see also...

- Construction and Assembly Instructions → page 1261
- List of Cam Latch / Cam Lock Types → page 1256
- Cam Latches GN 115 (Stainless Steel, with Operating Elements) → page 1266
- Cam Latches GN 115 (Stainless Steel, Operation with Socket Key) → page QVX

Accessory

- Protective caps GN 120
→ www.jwwinco.com
- Opening handles GN 120.1
→ www.jwwinco.com
- Protective guide plates GN 120.2
→ www.jwwinco.com
- Sheet metal punches GN 123 → page XYZ

On request

- Latch arm in A4
- Lock with different combinations

How to order

GN 115-SC-40-NI

1	Type
2	Latch arm distance A
3	Material