



- 1 Type**
- DK** With triangular spindle
 - VK7** With square spindle
 - VK8** With square spindle
 - SCH** With slot
 - VDE** With double bit
 - SK10** With hex

Metric table

2

Dimensions in: millimeters - inches

Latch arm distance A											d	h
4	8	13	16	20	24	28	32	36	40	45	28	4
0.16	0.31	0.51	0.63	0.79	0.94	1.10	1.26	1.42	1.57	1.77	1.10	0.16
6	10	14	18	22	26	30	34	38	42	50	28	4
0.24	0.39	0.55	0.71	0.87	1.02	1.18	1.34	1.50	1.65	1.97	1.10	0.16

Specification

3

- Cam latch housing
Zinc die-cast
- Housing collar
- Chrome plated finish —
- Powder coated ● **SW**
Black, RAL 9005, textured finish
- Latch arm / assembly hardware
Steel, zinc plated, blue passivated finish
- Protection class IP65
- IP Protection Classes → page XYZ
- RoHS compliant

Information

GN 115 cam latches lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 50 mm. Product comes supplied with a loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → page 1261
- List of Cam Latch / Cam Lock Types → page 1256
- Cam Latches GN 115 (Zinc Die-Cast, with Operating Elements) → page 1260
- Cam Latches GN 115 (Stainless Steel, Operation with Socket Key) → page 1267
- Cam Latches GN 515 (Zinc Die-Cast, with Extended Housing) → page XYZ

Accessory

- Socket keys GN 119.2 → page 1310
- Protective caps GN 120
→ www.jwwinco.com
- Opening handles GN 120.1
→ www.jwwinco.com
- Protective guide plates GN 120.2
→ www.jwwinco.com
- Internal cabinet handles GN 120.3 → page XYZ
- Sheet metal punches GN 123 → page XYZ

On request

- Other operations

How to order (Chrome plated housing collar)	1	Type
GN 115-VK8-20	2	Latch arm distance A

How to order (Powder coated housing collar)	1	Type
GN 115-SCH-32-SW	2	Latch arm distance A
	3	Finish (Housing collar)