



- 2** **Type**
- DK6.5** With triangular spindle h = 6.5
 - DK7** With triangular spindle h = 7
 - VK6** With square spindle A/F6
 - VK7** With square spindle A/F7
 - VK8** With square spindle A/F8
 - VDE5** With double bit d₂ = 5.6
 - SCH** With blade / slot

Metric table

Dimensions in: millimeters - inches

1												
l₁	l₂	b	d₁	d₂	h	s	A/F	Type				For cam latches
55 2.17	34 1.34	32 1.26	11.4 0.45	-	6.5 0.26	1.3 0.05	6	DK6.5	VK6	-	SCH	GN 115.1 / GN 115.6
86 3.39	53 2.09	50 1.97	14 0.55	5.6 0.22	7 0.28	1.8 0.07	7	DK7	VK7	VDE5	SCH	GN 115 / GN 115.7 / GN 115.8 / GN 115.10 / GN 116.1 GN 119 / GN 119.3 / GN 515 / GN 516 / GN 516.1 / GN 516.5
86 3.39	53 2.09	50 1.97	14 0.55	-	-	-	8	-	VK8	-	-	GN 115 / GN 115.7 / GN 115.8 / GN 115.10 / GN 116.1 GN 119 / GN 119.3 / GN 515 / GN 516 / GN 516.1 / GN 516.5

Specification

- Zinc die-cast
Powder coated
Black, RAL 9005, textured finish **● SW**
- RoHS compliant

How to order

GN 119.2-86-VK8-SW

1	Length l ₁
2	Type
3	Color