



**2 Type**  
**D** Consisting of three parts  
**Z** Consisting of two parts

**Metric table**

Dimensions in: millimeters - inches

s	b	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	l <sub>6</sub>	m <sub>1</sub>	m <sub>2</sub>
12 0.47	15 0.59	M 6	6 0.24	39.2 1.54	25.6 1.01	10 0.39	5 0.20	14 0.55	9 0.35	10 0.39	5 0.20	27.2 1.07	13.6 0.54
16 0.63	20 0.79	M 8	8 0.31	49 1.93	32.5 1.28	14 0.55	8 0.31	22 0.87	16 0.63	14 0.55	8 0.31	33 1.30	16.5 0.65

**Specification**

- Body  
Steel, zinc plated, blue passivated finish
- Pin  
Brass, nickel plated
- Washers  
Brass, nickel plated
- Hex nut ISO 4032  
Steel, zinc plated, blue passivated finish
- Serrated washer DIN 6797  
Steel, zinc plated, blue passivated finish
- RoHS compliant

**Information**

GN 129 hinges are used for hatch type doors. The hinges are normally arranged to the side of the door. In the two-part design, the door can be unhinged with two identically arranged hinges. The three-part hinges, which generally cannot be unhinged, are especially suitable for tamper-proof doors and flaps. When mounted inside, the hinges are not removable from the outside and therefore protect against manipulation.

see also...

- List of Hinge Types → page 1324
- Hinges GN 129.2 (Steel or Stainless Steel) → page 1359
- Hinges GN 129.3 (Steel) → www.jwwinco.com

How to order <b>GN 129-16-D</b>	1	Square s
	2	Type