



- 4 Identification no.**
2 With 4 stainless steel socket cap screws DIN 912

Metric table

1 d ₁ Bore	1 s ₁ Square	2 d ₂ Bore	2 s ₂ Square	3 k Clamping length	l ₁	l ₂	l ₃	m	z Screw locations for screw size	Accessory Recommended lever GN 911 for z l ₄
B 20	V 20	B 20	V 20	50 1.97	120 4.72	68 2.68	46 1.81	86 3.39	M8-35	63 2.48 78 3.07
B 25	V 25	B 25	V 25	50 1.97	120 4.72	68 2.68	46 1.81	86 3.39	M8-35	63 2.48 78 3.07
B 30	V 30	B 30	V 30	50 1.97	120 4.72	68 2.68	46 1.81	86 3.39	M8-35	63 2.48 78 3.07
B 30	V 30	B 30	V 30	60 2.36	141 5.55	79 3.11	59 2.32	101.5 4.00	M8-50	63 2.48 78 3.07
B 32	-	B 32	-	60 2.36	141 5.55	79 3.11	59 2.32	101.5 4.00	M8-50	63 2.48 78 3.07
B 35	V 35	B 35	V 35	60 2.36	141 5.55	79 3.11	59 2.32	101.5 4.00	M8-50	63 2.48 78 3.07
B 40	V 40	B 40	V 40	60 2.36	141 5.55	79 3.11	59 2.32	101.5 4.00	M8-50	63 2.48 78 3.07
B 40	V 40	B 40	V 40	76 2.99	176 6.93	98 3.86	70 2.76	127 5.00	M10-60	78 3.07 92 3.62
B 42	-	B 42	-	76 2.99	176 6.93	98 3.86	70 2.76	127 5.00	M10-60	78 3.07 92 3.62
B 45	V 45	B 45	V 45	76 2.99	176 6.93	98 3.86	70 2.76	127 5.00	M10-60	78 3.07 92 3.62
B 48	-	B 48	-	76 2.99	176 6.93	98 3.86	70 2.76	127 5.00	M10-60	78 3.07 92 3.62
B 50	V 50	B 50	V 50	76 2.99	176 6.93	98 3.86	70 2.76	127 5.00	M10-60	78 3.07 92 3.62

Dimensions in: millimeters - inches

Specification

- Body
Aluminum
- Powder coated
Black, RAL 9005, textured finish **● SW**
- Plain, matte shot-blasted finish **○ BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Accessory

- Adjustable levers GN 911 → page QVX

Information

The clamping bores of GN 194 T-angle connector clamps are not machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

The versions with square bores are also suitable for use with **profile systems**.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

see also...

- *Product Family Standard Parts for Profile Systems* → page QVX

How to order	
1	Bore d ₁ (Square s ₁)
2	Bore d ₂ (Square s ₂)
3	Clamping length k
4	Identification no.
5	Finish

GN 194-¹B20-²B20-³50-⁴2-⁵BL