



Metric



Metric table



Dimensions in: millimeters / inches

d ₁	d ₂	d ₃	h	Length l ±0.25	t min.
18 0.71	M 6	12 0.47	42 1.65	100 3.94	12 0.47
20 0.79	M 8	14 0.55	47 1.85	112 4.41	15 0.59
22 0.87	M 10	16 0.63	53 2.09	125 4.92	18 0.71
25 0.98	M 12	18 0.71	59 2.32	140 5.51	20 0.79

Specification



Cast iron (GS45)

- Powder coated
- Black, RAL 9005, textured finish
- Plain, tumbled finish
- Unfinished casting, deburred
- Contact surface machined

- SW
- BL

RoHS

Cabinet U-handles GN 225 are of simple and solid design. They are best chosen when handles need to be plated or painted. The tapped holes and contact faces are square and parallel.

see also...

GN 425 Cabinet U-Handles (Steel)

Page

QVX

Technical Information

Load Capacity Information

QVX

How to order

GN 225-20-SW

1 Handle diameter d₁

2 Finish