



Metric



SS Stainless Steel

Metric table



Dimensions in: millimeters / inches

d ₁	d ₂	d ₃	h ₁	h ₂
20 0.79	17 0.67	1.8 0.07	3.2 0.13	1.2 0.05
25 0.98	21 0.83	2.2 0.09	3.2 0.13	1.2 0.05
30 1.18	24 0.94	3.2 0.13	3.2 0.13	1.2 0.05
40 1.57	34.5 1.36	3.2 0.13	3.2 0.13	1.2 0.05
50 1.97	43 1.69	3.2 0.13	3.2 0.13	1.2 0.05

Specification



Stainless steel AISI 303

NI

RoHS

Adjustment plates GN 2277.1 are used in combination with GN 2277, Type A bull's eye spirit levels.

The mounting bore holes offset by 120° allow the bull's eye spirit levels and the mounting plate to be aligned in relation to the mounting surface. An alignment ball at the bottom surface of the adjustment plate serves as a tilting point.

Specific tightening torques of the bolts are allowed to be achieved, so that the bubble is centrally located inside the marking ring once the horizontal alignment is reached.

see also...

Page

GN 2277 Bull's Eye Spirit Levels

QVX

GN 2280 Bull's Eye Spirit Levels (Adjustable)

QVX

Technical Information

General Information on Bull's Eye, Screw-On and Cross Spirit Levels

QVX

Stainless Steel Characteristics

QVX

How to order

GN 2277.1-NI-30

1 Material

2 Outside diameter d₁

