


Metric



4 Sensitivity

- 6 Angular minutes, bubble moves by 2 mm
- 50 Angular minutes, bubble moves by 2 mm

5 Identification no.

- 1 Viewing window top
- 2 Viewing window top - front
- 3 Viewing window top - front - back

Metric table

2

Dimensions in: millimeters / inches

l_1	b	d	h_1	h_2	l_2	m
57 2.24	12 0.47	4.5 0.18	13 0.51	1 0.04	37 1.46	45 1.77

Specification

1 3

Housing

- Brass
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

● MSW
● MSR

Spirit level element

- Glass plastic body
- Filling
- Green transparent

G

Casting compound

Mineral-based

RoHS

On request

- Colorless transparent filling
- Other sensitivities
- Other colors

Screw-on spirit levels GN 2282 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

The spirit levels are aligned in relation to the finished reference surface so that the bubble is centered in the middle of the marking lines once the horizontal position of the contact surface in the longitudinal direction is reached.

see also...

	Page
GN 2283 Screw-On Spirit Levels (with Mounting Holes)	QVX
GN 2276 Cross Spirit Levels (with Mounting Holes)	QVX
GN 2280 Bull's Eye Spirit Levels (Adjustable)	QVX

Technical Information

General Information on Bull's Eye, Screw-On and Cross Spirit Levels	QVX
---	-----

How to order

1	Color
2	Length l_1
3	Filling
4	Sensitivity
5	Identification no.

1 2 3 4 5
GN 2282-MSR-57-G-50-3

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

