

Metric table

2 3

Dimensions in: millimeters - inches

| d ₁ | h ₉ | l ₁ | | | | | | d ₂ | d ₃ | d ₄ | d ₅ | l ₂ | l ₃ | l ₄ | l ₅ | l ₆ | l ₇ | s ₁ | s ₂ | Suitable key ring Ø for type E | Suitable spring cotter pins for identification no. 2 | | |
|----------------|----------------|----------------|------|------|------|------|------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|--------------------------------|--|------|------------------------|
| 8 | 0.31 | 16 | 20 | 24 | 28 | 30 | 32 | 2.5 | 12 | 2.5 | 4.3 | 5.5 | 7 | 13.5 | 18 | 10 | 2 | 3 | 4 | 14 | - | - | GN 1024-NI-2-D |
| | | 0.63 | 0.79 | 0.94 | 1.10 | 1.18 | 1.26 | 0.10 | 0.47 | 0.10 | 0.17 | 0.22 | 0.28 | 0.53 | 0.71 | 0.39 | 0.08 | 0.12 | 0.16 | 0.55 | - | - | GN 1024-NI-2-D |
| 8 | 0.31 | 35 | 40 | 45 | 50 | 55 | 60 | 2.5 | 12 | 2.5 | 4.3 | 5.5 | 7 | 13.5 | 18 | 10 | 2 | 3 | 4 | 14 | - | - | GN 1024-NI-2-D |
| | | 1.38 | 1.57 | 1.77 | 1.97 | 2.17 | 2.36 | 0.10 | 0.47 | 0.10 | 0.17 | 0.22 | 0.28 | 0.53 | 0.71 | 0.39 | 0.08 | 0.12 | 0.16 | 0.55 | - | - | GN 1024-NI-2-D |
| 10 | 0.39 | 20 | 24 | 30 | 35 | 40 | 45 | 2.5 | 15 | 2.5 | 4.3 | 6 | 7 | 15 | 21 | 11 | 4 | 3 | 4 | 14 | - | - | GN 1024-NI-2-E / ...-D |
| | | 0.79 | 0.94 | 1.18 | 1.38 | 1.57 | 1.77 | 0.10 | 0.59 | 0.10 | 0.17 | 0.24 | 0.28 | 0.59 | 0.83 | 0.43 | 0.16 | 0.12 | 0.16 | 0.55 | - | - | GN 1024-NI-2-E / ...-D |
| 10 | 0.39 | 50 | 55 | 60 | 65 | 70 | 80 | 2.5 | 15 | 2.5 | 4.3 | 6 | 7 | 15 | 21 | 11 | 4 | 3 | 4 | 14 | - | - | GN 1024-NI-2-E / ...-D |
| | | 1.97 | 2.17 | 2.36 | 2.56 | 2.76 | 3.15 | 0.10 | 0.59 | 0.10 | 0.17 | 0.24 | 0.28 | 0.59 | 0.83 | 0.43 | 0.16 | 0.12 | 0.16 | 0.55 | - | - | GN 1024-NI-2-E / ...-D |
| 12 | 0.47 | 20 | 24 | 30 | 35 | 40 | 45 | 2.5 | 17 | 3 | 5.3 | 7 | 9 | 18.5 | 23 | 12 | 4 | 4 | 4.5 | 14 | 18 | - | GN 1024-NI-2-E / ...-D |
| | | 0.79 | 0.94 | 1.18 | 1.38 | 1.57 | 1.77 | 0.10 | 0.67 | 0.12 | 0.21 | 0.28 | 0.35 | 0.73 | 0.91 | 0.47 | 0.16 | 0.16 | 0.18 | 0.55 | 0.71 | - | GN 1024-NI-2-E / ...-D |
| 12 | 0.47 | 50 | 55 | 60 | 65 | 70 | 80 | 2.5 | 17 | 3 | 5.3 | 7 | 9 | 18.5 | 23 | 12 | 4 | 4 | 4.5 | 14 | 18 | - | GN 1024-NI-2-E / ...-D |
| | | 1.97 | 2.17 | 2.36 | 2.56 | 2.76 | 3.15 | 0.10 | 0.67 | 0.12 | 0.21 | 0.28 | 0.35 | 0.73 | 0.91 | 0.47 | 0.16 | 0.16 | 0.18 | 0.55 | 0.71 | - | GN 1024-NI-2-E / ...-D |
| 16 | 0.63 | 32 | 35 | 40 | 45 | 50 | 55 | 3.5 | 22 | 3 | 5.3 | 8 | 9 | 21 | 28 | 15 | 6 | 4 | 4.5 | 14 | 18 | - | GN 1024-NI-3-E / ...-D |
| | | 1.26 | 1.38 | 1.57 | 1.77 | 1.97 | 2.17 | 0.14 | 0.87 | 0.12 | 0.21 | 0.31 | 0.35 | 0.83 | 1.10 | 0.59 | 0.24 | 0.16 | 0.18 | 0.55 | 0.71 | - | GN 1024-NI-3-E / ...-D |
| 16 | 0.63 | 60 | 65 | 70 | 80 | 90 | 100 | 3.5 | 22 | 3 | 5.3 | 8 | 9 | 21 | 28 | 15 | 6 | 4 | 4.5 | 14 | 18 | - | GN 1024-NI-3-E / ...-D |
| | | 2.36 | 2.56 | 2.76 | 3.15 | 3.54 | 3.94 | 0.14 | 0.87 | 0.12 | 0.21 | 0.31 | 0.35 | 0.83 | 1.10 | 0.59 | 0.24 | 0.16 | 0.18 | 0.55 | 0.71 | - | GN 1024-NI-3-E / ...-D |
| 20 | 0.79 | 40 | 45 | 50 | 55 | 60 | 65 | 4.5 | 26 | 3.5 | 6.4 | 10.5 | 9 | 24 | 31 | 17 | 6 | 4 | 5 | 14 | 18 | 24 | GN 1024-NI-4-E / ...-D |
| | | 1.57 | 1.77 | 1.97 | 2.17 | 2.36 | 2.56 | 0.18 | 1.02 | 0.14 | 0.25 | 0.41 | 0.35 | 0.94 | 1.22 | 0.67 | 0.24 | 0.16 | 0.20 | 0.55 | 0.71 | 0.94 | GN 1024-NI-4-E / ...-D |
| 20 | 0.79 | 70 | 80 | 90 | 100 | - | - | 4.5 | 26 | 3.5 | 6.4 | 10.5 | 9 | 24 | 31 | 17 | 6 | 4 | 5 | 14 | 18 | 24 | GN 1024-NI-4-E / ...-D |
| | | 2.76 | 3.15 | 3.54 | 3.94 | - | - | 0.18 | 1.02 | 0.14 | 0.25 | 0.41 | 0.35 | 0.94 | 1.22 | 0.67 | 0.24 | 0.16 | 0.20 | 0.55 | 0.71 | 0.94 | GN 1024-NI-4-E / ...-D |

Application example

