



2 Type

- U** For floating bearing rails
- X** For fixed bearing rails

Metric table

Dimensions in: millimeters - inches

1 h ₁ Rail	b ₁	b ₂	d For socket cap screw DIN 912	h ₂	l ₁	l ₂	l ₃ max.	m ₁	m ₂
18 0.71	12.6 0.50	5.6 0.22	M 3	17 0.67	7 0.28	5 0.20	3.5 0.14	-	3.5 0.14
28 1.10	19 0.75	10 0.39	M 4	25 0.98	7 0.28	5 0.20	3.5 0.14	8 0.31	4.5 0.18
35 1.38	25.5 1.00	12.5 0.49	M 4	32 1.26	7 0.28	5 0.20	3.5 0.14	10 0.39	5.5 0.22
43 1.69	32.2 1.27	15 0.59	M 4	40 1.57	7 0.28	5 0.20	3.5 0.14	12 0.47	7.5 0.30

Specification

- Wiper
Plastic PUR, gray
- Bracing core
Steel, zinc plated
- Socket cap screws DIN 912
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

GN 2428 wipers protect against dirt deposits on rails and rollers.
For size h₁ = 18 mm, the wiper is mounted with only one central screw.
Screws are included.

see also...

- [Cam Roller Linear Guide Rails GN 2422 → page 1925](#)
- [Cam Roller Carriages GN 2424 → page 1926](#)

How to order GN 2428-35-X	1 Height h ₁
	2 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10