

4 Type

A Without accessory

Metric table

1 s		2 Length l		3 n	b ₁	b ₂ *	h ₁	k
Nominal dimension	Actual dimension	Nominal dimension	Actual dimension		For screw	For screw		
30 1.18	28 1.10	30 1.18	27 1.06	8 0.31	M 6	-	5.5 0.22	-
30 1.18	28 1.10	60 2.36	57 2.24	8** 0.31	M 6	-	6 0.24	-
40 1.57	38 1.50	40 1.57	36 1.42	10 0.39	M 8	-	5.5 0.22	-
40 1.57	36 1.42	80 3.15	80 3.15	10** 0.39	M 8	-	9 0.35	-
45 1.77	42 1.65	45 1.77	41 1.61	10 0.39	M 8	-	9 0.35	-
45 1.77	42 1.65	90 3.54	87 3.43	10** 0.39	M 8	-	9.5 0.37	-
60 2.36	56 2.20	60 2.36	57 2.24	8** 0.31	M 6	M 8	6 0.24	30 1.18
80 3.15	74 2.91	80 3.15	76 2.99	10** 0.39	M 8	-	8 0.31	40 1.57
90 3.54	88 3.46	90 3.54	86 3.39	10** 0.39	M 8	-	9.5 0.37	45 1.77

* Slotted holes only on 60608 ** Additional guide steps for further slot widths

Specification

- Angle bracket
Aluminum
- Painted, white aluminum
- Plain finish



AW
AB

- RoHS

Accessory

- T-nuts GN 50b → page QVX
- T-slot nuts GN 51b → page QVX
- T-slot bolts GN 52b → page QVX
- Collar nuts GN 53b → page QVX

Information

Angle brackets GN 30b fasten aluminum profiles to objects such as tables and panels or at right angles to each other. Machining of the profile is not necessary.

The connection can be freely positioned and slid along the slot. To fasten the angle brackets to a panel or transversely to an aluminum profile, the guide steps must be broken off.

see also...


- Aluminum Profiles GN 10b (Profile Type Light) → page QVX
- Aluminum Profiles GN 10b (Profile Type Heavy) → page QVX

How to order	
1 Width s	
2 Length l	
3 Slot width n	
4 Type	
5 Finish	


GN 30b-30308-A-AW

Assembly Options / Application Examples

Assembly of cover cap



Use



Application examples

