


Inch | Metric



**3 Type**

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side



Inch table

1 2

Dimensions in: inches / millimeters

b <sub>1</sub>	l <sub>1</sub> ±0.02						a	b <sub>2</sub>	b <sub>3</sub>	d	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>2</sub> max.	l <sub>3</sub>	t min.
1.42	8.00	10.00	12.00	16.00	20.00	24.00	0.94	0.87	1.50	5/16 x 18	2.38	3.13	0.20	0.85	1.18	0.59
36.1	203.2	254	304.8	406.4	508	609.6	23.9	22.1	38.1		60.5	79.5	5.1	21.6	30	15

Metric table

1 2

Dimensions in: millimeters / inches

b <sub>1</sub>	l <sub>1</sub> ±0.5						a	b <sub>2</sub>	b <sub>3</sub>	d	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>2</sub> max.	l <sub>3</sub>	t min.		
36	200	250	300	350	400	500	600	800	24	22	38	M 8	60.5	79.5	5	16.5	25	15
1.42	7.87	9.84	11.81	13.78	15.75	19.69	23.62	31.50	0.94	0.87	1.50		2.38	3.13	0.20	0.65	0.98	0.59

Specification **4**

**Tube**

Aluminum

- Powder coated
  - Black, RAL 9005, textured finish **● SW**
- Anodized finish, natural color **● EL**
- Anodized finish, natural color **● ES**
- Handle legs black
- Handle legs silver

**Handle legs**

Zinc die-cast

Powder coated, textured finish

- Black, RAL 9005 for SW / EL
- Silver, RAL 9006 for ES

**Cover**

Plastic, light gray

**Mounting set (Type B)**

Stainless steel

- Socket button head screws ISO 7380-M8-30
- Hex nuts ISO 4032
- Washers DIN 125

RoHS

Oval tubular handles GN 335 have an inclined handle profile with a 45° angle. These handles are comfortable and ergonomic to grasp in a variety of applications such as sliding doors.

In Type B, socket button head screws, hex nuts and washers are included parts of the order.

The tubular handle can be screwed onto the handle shanks without further modification. This allows even a small quantity of special lengths to be ordered.

see also...

	Page
GN 334 Oval Tubular Handles (Mounting from the Back)	QVX
GN 334.1 Oval Tubular Handles (Mounting from the Operator's Side)	QVX

**Technical Information**

Load Capacity Information

QVX

How to order (Inch)

1	Handle diameter b <sub>1</sub>
2	Length l <sub>1</sub>
3	Type
4	Finish

**GN 335-1.42-12.00-A-EL**

How to order (Metric)

1	Handle diameter b <sub>1</sub>
2	Length l <sub>1</sub>
3	Type
4	Finish

**GN 335-36-200-A-EL**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

