



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Pilot hole	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃
110 4.33	P 8	26 1.02	37 1.46	23 0.91	55 2.17	48 1.89	0.4 0.02

Specification

- Three-lobed knob
Phenolic plastic
 - Temperature resistant up to 300 °F (150 °C)
 - Black, shiny finish
- Hub insert
Steel
 - Zinc plated
 - Molded-in
- *Plastic Characteristics* → page QVX
- [RoHS compliant](#)

On request

- Stainless steel insert
- Special inch or metric size bores, threads, or glued in threaded studs

Information

3P-A three-lobed knobs are a great choice for heavy duty applications. The pilot hole in the solid steel insert provides greater flexibility for mounting options.

How to order ¹ ² 3P-A-110-P8	1 Handle diameter d ₁
	2 Pilot hole d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

