



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂		d ₃	h ₁	h ₂	h ₃	s	t
34 1.34	M 6	-	17 0.67	22 0.87	20 0.79	12 0.47	7 0.28	9 0.35
45 1.77	M 8	-	25 0.98	30 1.18	27 1.06	18 0.71	8.5 0.33	14 0.55
65 2.56	M 8	-	30 1.18	39 1.54	36 1.42	25 0.98	10 0.39	14 0.55
65 2.56	M 10	-	30 1.18	39 1.54	36 1.42	25 0.98	10 0.39	15 0.59
85 3.35	M 8	M 10	35 1.38	48 1.89	43 1.69	30 1.18	12 0.47	17 0.67

Specification

- Three-lobed knob
Phenolic plastic
- Temperature resistant up to 300 °F (150 °C)
- Black, shiny finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

3P-B three-lobed knobs have an aesthetically pleasing shape and provide a comfortable grip. Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Three Lobed Knobs 3P-P (with Steel Threaded Stud)* → page 652

How to order ¹ ² 3P-B-85-M8	1	Handle diameter d ₁
	2	Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4