



Metric



Metric table

d ₁	Length l								d ₂	d ₃	h	r	t min.
	32	45	55*	64	88*	-	-	-					
6 0.24	1.26	1.77	2.17	2.52	3.46	-	-	M 3	9 0.35	26 1.02	7 0.28	6 0.24	
8 0.31	55*	64	88*	96	100	120*	128	M 4	12 0.47	35 1.38	10 0.39	8 0.31	
10 0.39	88*	100	120*	180*	200	235*	-	M 5	15 0.59	43 1.69	12 0.47	12 0.47	
12 0.47	125	160	200	250	-	-	-	M 6	-	51 2.01	14 0.55	12 0.47	
16 0.63	160	200	250	300	-	-	-	M 6	-	59 2.32	18 0.71	12 0.47	

* Suitable for 19" rack and enclosure layout

Specification

Handle

- Steel
- Powder coated
 - Black, RAL 9005, textured finish
 - Chrome plated
 - Blackened finish

- SW
- CR
- BT

Location disks

Zinc die-cast, nickel-plated finish

RoHS

On request

- Various metric size fasteners and kit packaging

Cabinet U-handles GN 425 are manufactured from a bent steel profile. Cabinet U-handles GN 425 with Ø d₁ = 6, 8 and 10 mm are supplied with two location disks to guarantee a perfect location even with large holes in the cabinet. The location disks are enclosed in the package with the handle. The stainless steel version is preferred over the chrome plated version for outdoor applications.

see also...

	Page
GN 425 Cabinet U-Handles (Aluminium / Stainless Steel)	QVX
GN 425.1 Cabinet U-Handles (Offset Round Steel)	QVX

Technical Information

Load Capacity Information	QVX
---------------------------	-----

Accessory

GN 181 Mounting Plate Sets (Mounting from the Operator's Side)	QVX
--	-----

How to order

GN 425-10-120-CR

1	Handle diameter d ₁
2	Length l
3	Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

