



4 Type

C With fastening set

Metric table

1 l_1	2 n_1	3 n_2	d	l_2	l_3	m	A/F in mm
24 0.94	6 0.24	6 0.24	M 6	27 1.06	27 1.06	15 0.59	4
32 1.26	8 0.31	8 0.31	M 8	36 1.41	36 1.41	20 0.79	5

Dimensions in: millimeters - inches

Specification

- Housing
Zinc die-cast
Painted, white aluminum **ZW**
- Fastening set
Screws and T-nut
Steel, zinc plated, blue passivated finish **SZ**
- **RoHS**



Information

Rotating angle brackets GN 42i connect two crossed profiles at an any angle. Machining of the profile is not necessary.

Loosening the screw simultaneously adjusts the angle and position along the grooves.

see also...

- Aluminum Profiles GN 10i (Profile Type Light) → page QVX
- Aluminum Profiles GN 10i (Profile Type Heavy) → page QVX
- Aluminum Profiles GN 11i (with Partially Closed Slots) → page QVX

How to order

GN 42i-32 8 8 -C-ZWSZ

1	Length l_1
2	Slot width n_1
3	Slot width n_2
4	Type
5	Finish (Housing)
6	Material / Finish (Fastening set)