



Metric



SS Stainless Steel

Metric table

Dimensions in: millimeters / inches

d ₁	Length l ±0.5			h		d ₂	r	t min.
12 0.47	125 4.92	160 6.30	200 7.87	75 2.95	110 4.33	M 6	14 0.55	12 0.47
16 0.63	160 6.30	200 7.87	300 11.81	85 3.35	125 4.92	M 6	18 0.71	12 0.47

Specification

Stainless steel AISI 303	NI	GS
• Matte shot-blasted finish		
• Powder coated		
• Black, RAL 9005, textured finish	● SW	

RoHS

On request

- Other dimensions
- Other materials
- Other finishes

Cabinet U-handles GN 435 in tall design are made from bent round profiles and are designed for applications requiring a greater height for gripping. For example, this makes it possible to grab or hold the handle while wearing safety gloves. Some dimensions also comply with the crane access standard DIN EN 13856.

In addition to serving as a handle, they can also be used as hose guides, retaining brackets or similar.

see also...	Page
GN 425 Cabinet U-Handles	QVX
GN 435.3 Cabinet U-Handles (Weldable)	QVX
GN 426.5 Cabinet U-Handles	QVX
GN 426.3 Tubular Cabinet U-Handles (Steel, Weldable)	QVX
GN 565.5 Cabinet U-Handles	QVX

Technical Information

Load Capacity Information	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 181 Mounting Plate Sets (Mounting from the Operator's Side)	QVX
--	-----

How to order

1	Material
2	Handle diameter d ₁
3	Length l
4	Height h
5	Finish

GN 435-NI-12-160-75-SW

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

