



SS Stainless Steel

**3 Type**

- A** With arrow
- B** Neutral, without arrow or scale
- S** With standard scale 0...9  
20 graduations

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> $d_1$	<b>2</b> $d_2$ H8 Bore		$d_3$	$d_4$	$h_1$	$h_2$	Length $l$	$t$ min.
24 <i>0.94</i>	B 5	B 6	22 <i>0.87</i>	M 4	24 <i>0.94</i>	8 <i>0.31</i>	12 <i>0.47</i>	18 <i>0.71</i>
28 <i>1.10</i>	B 6	B 8	26 <i>1.02</i>	M 4	27 <i>1.06</i>	9 <i>0.35</i>	13 <i>0.51</i>	20 <i>0.79</i>

**Specification**

**4**

- Stainless steel AISI 304  
Matte shot-blasted finish **MT**
- Scale (Type S) and arrow (Type A)  
Laser engraved
- Socket set screw DIN 916  
Stainless steel  
with internal hex and serrated point
- *ISO Fundamental Tolerances* → page QVX
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

**On request**

- Special graduations  
see "How to order Graduations" → page QVX

**Information**

GN 436.1 knurled control knobs have graduation scales or arrow markings that are abrasion-resistant and easy to read.

Besides the standard scale (Type S) the control knobs can be supplied with any type of graduation.

Regarding design, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order sheet "How to order Graduations".

**How to order**

**GN 436.1-28-B6-S-MT**

- 1** Outside diameter  $d_1$
- 2** Bore  $d_2$
- 3** Type
- 4** Finish