



Metric



elesa
Original design M.243

Metric table



Dimensions in: millimeters / inches

Length l	a	b	d	h	t min.
86 ±0.5 3.39 ±0.02	17 0.67	26 1.02	M 6	43 1.69	12 0.47
117 ±0.5 4.61 ±0.02	20 0.79	30 1.18	M 8	54 2.13	13 0.51
179 ±1.0 7.05 ±0.04	20 0.79	30 1.18	M 8	62 2.44	13 0.51

Specification

Handle

Plastic, Phenolic (PF)

- Operating temperature
-22 °F to +248 °F (-30 °C to +120 °C)
- Black, shiny finish
- Flash mark cleaned and polished

• Tapped inserts

Brass

RoHS

On request

- Various metric size fasteners and kit packaging

Cabinet U-handles EN 525 have an ergonomic design and aesthetically appealing shiny finish.

see also...

GN 565 Cabinet U-Handles (Aluminum)

Page

QVX

Technical Information

Strength Values

QVX

Plastic Characteristics

QVX

How to order

EN 525-117

1 Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

