



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	d ₃	h +0.5	k	t min.
22 0.87	M 6	13 0.51	25 0.98	13 0.51	12 0.47
25 0.98	M 8	16 0.63	28 1.10	14 0.55	13 0.51
32 1.26	M 10	19 0.75	32 1.26	15 0.59	17 0.67

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 194 °F (90 °C)
- White, RAL 9002, painted, shiny finish **WS**
- Tapped insert
Stainless steel AISI 303
- *Stainless Steel Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

The surface quality of EN 530.1 knurled nuts is of a sufficiently high standard to meet the highest requirements. Flash marks are not visible.

The smooth and closed surfaces comply with requirements for hygienic applications. Duroplast material is highly resistant to chemicals.

<p>How to order</p> <p>¹ ² ³</p> <p>EN 530.1-25-M8-CL</p>	1 Handle diameter d ₁
	2 Thread d ₂
	3 Color