



**SS** Stainless Steel

**3 Type**

- A** With lanyard ring only
- H** With retaining cable
- K** With ball chain

**Metric table**

Dimensions in: millimeters - inches

<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>h<sub>3</sub></b>	<b>r ≈</b>	<b>s</b>	<b>t min.</b>
40 1.57	M 8	14 0.55	24 0.94	12 0.47	3.2 0.13	22.3 0.88	2.8 0.11	15 0.59
50 1.97	M 10	18 0.71	30 1.18	17 0.67	3.9 0.15	29.6 1.17	3.2 0.13	18 0.71
60 2.36	M 12	20 0.79	38 1.50	20 0.79	3.9 0.15	30.7 1.21	3.2 0.13	22 0.87

**Specification**

- Star knob  
Stainless steel AISI 316L  
- Hub welded  
- Matte shot-blasted finish
- Tapped insert  
Stainless steel AISI 304
- Lanyard ring GN 111.6  
Stainless steel AISI 301
- Ball chain GN 111.5 (Type K)  
Stainless steel AISI 301
- Retaining cable GN 111.2 (Type H)  
Stainless steel  
Coated with clear plastic
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

**Information**

- GN 5334.13 star knobs with loss protection can be attached to a base element with the help of a ball chain or a retaining cable.
- The star knobs are supplied ready assembled (with lanyard ring, with lanyard ring and retaining cable, or with lanyard ring and ball chain).
- see also...**
- [Ball Chains GN 111.5 \(Stainless Steel\)](#) → page 1236
  - [Retaining Cables GN 111.2 \(Stainless Steel\)](#) → page 1238
  - [Spiral Retaining Cables GN 111.4](#) → page 1237
  - [Lanyard Rings GN 111.6 \(Stainless Steel\)](#) → page 1241
  - [More Star Knobs with Loss Protections GN 111.7](#) → page 2046

**On request**

- Ball chains / retaining cables with other lengths
- With spiral retaining cable GN 111.4
- Other GN / DIN series with loss protection

<b>How to order</b>	<b>1</b> Handle diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>
	<b>3</b> Type

**GN 5334.13-40-M8-H**