



Metric table

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.	
	MS Insert	NI Insert					
63 2.48	M 8	M 10	M 8	23 0.91	30.5 1.20	16 0.63	13 0.51
80 3.15	M 10	M 12	M 10	30.5 1.20	37 1.46	20 0.79	17 0.67
100 3.94	M 12	M 14	M 12	35 1.38	43 1.69	23 0.91	20 0.79

Specification

- Three-lobed knob  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black, matte finish

- Tapped insert  
- Brass **MS**  
- Stainless steel AISI 303 **NI**

- Color of the cover cap (matte finish):  
Black, RAL 9005 ● **DSW**  
Orange, RAL 2004 ● **DOR**  
Gray, RAL 7035 ● **DGR**  
Yellow, RAL 1021 ● **DGB**  
Blue, RAL 5024 ● **DBL**  
Red, RAL 3000 ● **DRT**  
Green, RAL 6017 ● **DGN**

- Plastic Characteristics → page QVX
- Stainless Steel Characteristics → page QVX

• RoHS compliant

Information

The ergonomic shape of the EN 533 three-lobed knobs supports effective gripping, resulting in a high torque.

see also...

- Three-Lobed Knobs GN 5345 → page QVX
- Three-Lobed Knobs EN 5330 (Plastic) → page QVX

How to order	
1	Handle diameter d <sub>1</sub>
2	Thread d <sub>2</sub>
3	Insert material
4	Color of the cover cap

EN 533-63-M8-MS-DSW