



Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	<sup>3</sup> Length l	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
63 2.48	M 8	25 0.98	23 0.91	30.5 1.20	16 0.63
80 3.15	M 10	30 1.18	30.5 1.20	37 1.46	20 0.79
100 3.94	M 12	40 1.57	35 1.38	43 1.69	23 0.91

Specification

- Three-lobed knob  
Plastic  
Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 266 °F (130 °C)
  - Black, matte finish
- Threaded stud  
Steel zinc plated, blue passivated finish
- Color of the cover cap (matte finish):
 

● DSW	Black, RAL 9005
● DOR	Orange, RAL 2004
● DGR	Gray, RAL 7035
● DGB	Yellow, RAL 1021
● DBL	Blue, RAL 5024
● DRT	Red, RAL 3000
● DGN	Green, RAL 6017
- Plastic Characteristics → page QVX
- RoHS compliant

Information

The ergonomic shape of the EN 533 three-lobed knobs with threaded stud supports effective gripping, resulting in a high torque.

see also...

- Three-Lobed Knobs GN 5345 → page QVX
- Three-Lobed Knobs EN 5330 (Plastic) → page QVX

How to order	
<sup>1</sup>	1 Handle diameter d <sub>1</sub>
<sup>2</sup>	2 Thread d <sub>2</sub>
<sup>3</sup>	3 Length l
<sup>4</sup>	4 Color of the cover cap

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**EN 533-100-M12-40-DSW**

1.1 1.2 1.3 1.4 2.1 2.2 2.3 2.4