



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

| 1 d ₁ | 2 d ₂ | 3 Length l | | | d ₃ | h | k | t min. |
|----------------------------|----------------------------|----------------------|------------|------------|----------------|------------|--------------|------------|
| 20 0.79 | M 5 | 10 0.39 | 16 0.63 | - | 14 0.55 | 13 0.51 | 8.5 0.33 | 8 0.31 |
| 24 0.94 | M 6 | 16 0.63 | 20 0.79 | 25 0.98 | 16 0.63 | 15 0.59 | 10.5 0.41 | 9 0.35 |
| 28 1.10 | M 8 | 16 0.63 | 20 0.79 | 30 1.18 | 18 0.71 | 17 0.67 | 12.5 0.49 | 10 0.39 |

Specification

- Stainless steel AISI 304
 - Matte shot-blasted finish **MT**
 - Highly polished finish **PL**
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

The knurl design with no underside grooves makes the GN 535 knurled screws and GN 536 knurled nuts an appropriate choice for hygienic applications.

see also...

- Knurled Nuts DIN 6303 (Stainless Steel) → page 699
- Knurled Nuts DIN 466 (Stainless Steel) → page 704
- Knurled Thumb Screws DIN 464 (Stainless Steel) → page 705

| | |
|---|---|
| How to order (Screw) GN 535-28-M8-20-MT | 1 Handle diameter d ₁ |
| | 2 Thread d ₂ |
| | 3 Length l |
| | 4 Finish |
| How to order (Nut) GN 536-20-M5-PL | 1 Handle diameter d ₁ |
| | 2 Thread d ₂ |
| | 4 Finish |