



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	d ₃	d ₄	h ₁	h ₂	t min.
40 1.57	M 6	18 0.71	18.8 0.74	30.5 1.20	15 0.59	12 0.47
40 1.57	M 8	18 0.71	18.8 0.74	30.5 1.20	15 0.59	15 0.59
50 1.97	M 8	21 0.83	21.8 0.86	34 1.34	17 0.67	15 0.59
50 1.97	M 10	21 0.83	21.8 0.86	34 1.34	17 0.67	18 0.71

Specification

- Star knob
Stainless steel AISI 316L
- Matte finish (Ra < 0.8 µm) **MT**
- Polished finish (Ra < 0.8 µm) **PL**
- Sealing ring
- H-NBR **H**
Temperature resistant from -13 °F to +302 °F (-25 °C to +150 °C)
- EPDM **E**
Temperature resistant from -40 °F to +248 °F (-40 °C to +120 °C)
- Blue
- Hardness 85±5 shore A
- FDA compliant
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Accessory

- Sealing rings GN 7600 → page 1683

On request

- with FKM sealing ring (fluorine rubber) **F**

Information

GN 5435 star knobs are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish and the large corner radii prevent adherence of dirt and facilitate cleaning.

see also...

- Product Family **Hygienic Design** → page 16
- Three-Lobed Knobs GN 5445 (Stainless Steel, **Hygienic Design**) → page 642
- Adjustable Levers GN 305 (Stainless Steel, **Hygienic Design**) → page 434

How to order	
¹ Handle diameter d ₁	
² Thread d ₂	
³ Finish	
⁴ Sealing ring material	

GN 5435-40-M8-PL-H

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4