



Metric



2 Type

- A** Closed type
- B** Open-end type, mounting from the back (tapped blind hole)
- C** Open-end type, mounting from the operator's side

Metric table



Dimensions in: millimeters / inches

l_1	a_1	a_2	a_3	b_1	b_2	d_1	d_2	h_1	h_2	h_3	h_4	h_5	l_2	l_3 ± 0.2	l_4	l_5	l_6	l_7	t_1 min.	t_2 min.	t_3
162	38	19	40	25	28	M 8	8.3	55	57	36	38	28	128	140	8	22	10	20	12	16	8
6.38	1.50	0.75	1.57	0.98	1.10		0.33	2.17	2.24	1.42	1.50	1.10	5.04	5.512	0.31	0.87	0.39	0.79	0.47	0.63	0.31

Specification



Handle

Aluminum

Powder coated

- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

- **SW**
- **SR**

Cover cap for Type C

Plastic

- Black for SW
- Light gray for SR

RoHS

On request

- Various metric size fasteners and kit packaging

Open-end or closed-end type cabinet / door handles GN 559 are mainly used in applications requiring a sturdy and rugged grip.

A special characteristic of the GN 559 is the thumb rest pad on the front leg. The fastening bores of type C are closed by a cover cap following the handle installation. The cover cap is included in the delivery contents.

Cabinet U-handles GN 559 are known for their high stability. They are fixed by two 5/16" or M8 screws whereby type A offers two alternative hole centers (l_2 or l_3).

Technical Information

Load Capacity Information

Page

QVX

How to order

GN 559-162-B-SW

- 1** Length l_1
- 2** Type
- 3** Finish