



Metric



Metric table



Dimensions in: millimeters / inches

| d₁ Thread Ø of spring plungers GN 611 / GN 616 / GN 616.1 | | | | | | | | | |
|--|-----|-----|-----|-----|------|------|------|------|------|
| M 3 | M 4 | M 5 | M 6 | M 8 | M 10 | M 12 | M 16 | M 20 | M 24 |

Specification

Steel

RoHS

Installation tools GN 611.5 are used to install spring plungers GN 611, GN 616 and GN 616.1.

see also...

| | Page |
|---|-------------|
| GN 611 Long Stroke Spring Plungers | QVX |
| GN 616 Spring Plungers (Steel / Stainless Steel) | QVX / QVX |
| GN 616.1 Spring Plungers (Steel / Stainless Steel) | QVX |

How to order

GN611.5-M12

1 Thread d₁

