



Metric table

Dimensions in: millimeters - inches

d	l ₁	Metric bolt size	Inch bolt size	b ₁	b ₂	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄
6.6 .26	60 2.36	M 6	1/4	20 .79	10 .39	10 .39	9 .35	20 .79	20 .79	20 .79	8 .31
9 .35	80 3.15	M 8	5/16	25 .98	12 .47	12 .47	11 .43	24 .94	25 .98	25 .98	9 .35
11 .43	100 3.94	M 10	3/8	30 1.18	15 .59	15 .59	14 .55	30 1.18	32 1.26	32 1.26	12 .47
14 .55	125 4.92	M 14	1/2	40 1.57	20 .79	20 .79	18 .71	40 1.57	40 1.57	40 1.57	16 .63
18 .71	125 4.92	M 18	5/8	50 1.97	25 .98	25 .98	23 .91	50 1.97	49 1.93	40 1.57	20 .79
18 .71	160 6.30	M 18	5/8	50 1.97	25 .98	25 .98	23 .91	50 1.97	49 1.93	50 1.97	20 .79
22 .87	160 6.30	M 22	3/4	60 2.36	30 1.18	30 1.18	27 1.06	60 2.36	55 2.17	55 2.17	24 .94
22 .87	200 7.87	M 22	3/4	60 2.36	30 1.18	30 1.18	27 1.06	60 2.36	55 2.17	70 2.76	24 .94
26 1.02	200 7.87	M 24	1	70 2.76	35 1.38	35 1.38	32 1.26	70 2.76	72 2.83	60 2.36	28 1.10
26 1.02	250 9.84	M 24	1	70 2.76	35 1.38	35 1.38	32 1.26	70 2.76	72 2.83	80 3.15	28 1.10
33 1.30	250 9.84	M 30	1 1/4	80 3.15	40 1.57	40 1.57	35 1.38	80 3.15	91 3.58	80 3.15	40 1.57
33 1.30	315 12.40	M 30	1 1/4	80 3.15	40 1.57	50 1.97	45 1.77	100 3.94	91 3.58	100 3.94	40 1.57
43 1.69	400 15.75	M 42	1 1/2	100 3.94	50 1.97	60 2.36	55 2.17	120 4.72	105 4.13	120 4.72	50 1.97

Specification

- Goose neck clamps
Tempered steel, lacquer painted finish
- RoHS compliant

Accessory

- DIN 787 T-slot bolt → page QVX
- DIN 6330 fixture nut → page QVX
- DIN 6340 heavy duty flat washer → page QVX
- DIN 508 T-slot nut → page QVX
- DIN 6379 double-ended threaded stud → page QVX

Information

DIN 6316 goose neck clamps with closed slot have a large offering of clamp size options. They range from 2.36" (60 mm) to 15.75" (400 mm) in length with the ability to clamp small to very large parts.

see also...

- Adjustable Goose Neck Clamps NO. 6316 V → page QVX
- Adjustable Plain Clamps NO. 6314 V → page QVX

How to order	1	Diameter d
	2	Length l ₁

DIN 6316-22-200