



SS Stainless Steel

Metric table

d ₁	d ₂	Length l ≈																		d ₃	h ₁	h ₂
		GN 6335.4									GN 6335.5											
		ST									SK											
32 1.26	M 6	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	45 1.77	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	45 1.77	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	14 0.55	20 0.79	10 0.39	
40 1.57	M 8	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	55 2.17	15 0.59	20 0.79	25 0.98	30 1.18	40 1.57	55 2.17	20 0.79	25 0.98	30 1.18	40 1.57	-	18 0.71	25 0.98	13 0.51	
50 1.97	M 10	25 0.98	30 1.18	35 1.38	45 1.77	55 2.17	-	25 0.98	30 1.18	35 1.38	45 1.77	55 2.17	-	20 0.79	25 0.98	30 1.18	45 1.77	55 2.17	22 0.87	32 1.26	20 0.79	
63 2.48	M 12	30 1.18	35 1.38	40 1.57	50 1.97	60 2.36	-	30 1.18	35 1.38	40 1.57	50 1.97	60 2.36	-	30 1.18	40 1.57	50 1.97	-	-	26 1.02	40 1.57	25 0.98	
80 3.15	M 16	-	-	-	-	-	-	30 1.18	40 1.57	50 1.97	60 2.36	70 2.76	-	-	-	-	-	-	35 1.38	50 1.97	30 1.18	

Dimensions in: millimeters - inches

Specification

- GN 6335.4**
 - Hand knob Plastic Technopolymer (Polyamide PA) Shock-resistant, black, matte finish **ST**
 - Hand knob Plastic Duroplast (Phenolic PF) Black, shiny finish **SK**
 - Threaded stud Steel, zinc plated, blue passivated finish

- GN 6335.5**
 - Hand knob Plastic Technopolymer (Polyamide PA) Shock-resistant, black, matte finish **ST**
 - Threaded stud Stainless steel M6 - M10: AISI 304 Cu M12: AISI 303
 - Hand knob Plastic Duroplast (Phenolic PF) Black, shiny finish **SK**
 - Threaded stud Stainless steel A2

- Plastic Characteristics → page 2135
- Stainless Steel characteristics → page 2143
- RoHS compliant

Information

GN 6335.4 and GN 6335.5 hand knobs comply with DIN 6335 type L.
see also...
• Hand Knobs GN 6335.4 / GN 6335.5 with Loss Protection GN 111.7 → page 2046

On request

- Special inch and metric size threaded studs and stud lengths

How to order (Steel threaded stud)	1 Material
1 2 3 4	2 Handle diameter d ₁
GN 6335.4-SK-80-M16-50	3 Thread d ₂
	4 Length l

How to order (Stainless steel threaded stud)	1 Material
1 2 3 4	2 Handle diameter d ₁
GN 6335.5-ST-50-M10-25	3 Thread d ₂
	4 Length l