



**SS** Stainless Steel

**4 Type**

- D** With tapped through bore
- E** With tapped blind bore

**Metric table**

Dimensions in: millimeters - inches

<b>2</b> d <sub>1</sub>	<b>3</b> d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t <sub>1</sub> min.	t <sub>2</sub>
32 1.26	M 6	12 0.47	20 0.79	9 0.35	12 0.47	10 0.39
40 1.57	M 8	14 0.55	25 0.98	12 0.47	15 0.59	13 0.51
50 1.97	M 10	18 0.71	32 1.26	15 0.59	18 0.71	16 0.63
63 2.48	M 12	20 0.79	40 1.57	19 0.75	22 0.87	20 0.79

**Specification**

- Stainless steel precision casting  
AISI 316 **A4**  
Polished finish **PL**
- [Stainless Steel Characteristics](#) → page QVX
- [RoHS compliant](#)

**Information**

Star knobs GN 6336 satisfy the dimensions of the DIN 6336 but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygienic requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- [Star Knobs DIN 6336 \(Plastic\)](#) → page QVX
- [Star Knobs DIN 6336 \(Cast Iron / Stainless Steel / Aluminum\)](#) → page QVX
- [Star Knobs GN 6336.1 \(Phenolic Plastic, with Protruding Hub\)](#) → page QVX
- [Star Knobs GN 6336.2 \(Technopolymer Plastic, with Protruding Hub\)](#) → page QVX

**How to order**

**GN 6336-A4-50-M10-D-PL**

<b>1</b>	Material
<b>2</b>	Handle diameter d <sub>1</sub>
<b>3</b>	Thread d <sub>2</sub>
<b>4</b>	Type
<b>5</b>	Finish