



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d₁ <small>+0.1 +0.3</small>	d₂ <small>-0.2</small>	s <small>±0.1</small>		
4 0.16	8 0.31	1 0.04	2 0.08	-
4 0.16	12 0.47	1 0.04	2 0.08	3 0.12
5 0.20	10 0.39	1 0.04	2 0.08	3 0.12
5 0.20	15 0.59	2 0.08	3 0.12	-
6 0.24	12 0.47	1 0.04	2 0.08	3 0.12
6 0.24	20 0.79	2 0.08	3 0.12	5 0.20
8 0.31	16 0.63	2 0.08	3 0.12	5 0.20
8 0.31	25 0.98	2 0.08	3 0.12	5 0.20
10 0.39	20 0.79	2 0.08	3 0.12	5 0.20
10 0.39	30 1.18	3 0.12	5 0.20	-
12 0.47	20 0.79	2 0.08	3 0.12	5 0.20
12 0.47	30 1.18	3 0.12	5 0.20	-
16 0.63	20 0.79	2 0.08	3 0.12	5 0.20
16 0.63	30 1.18	3 0.12	5 0.20	-

Specification

- Stainless steel AISI 304
- Turned
- Plain finish



NI

- Stainless Steel Characteristics → page QVX
- RoHS compliant

On request

- Other dimensions
- Chemically blackened surface

Information

GN 6343 washers / leveling disks are mainly used in mechanical machine and jig construction where shimming may be required for leveling.

see also...

- Countersunk Washers GN 184.5 → page QVX
- Heavy Duty Flat Washers DIN 6340 → page QVX
- Heavy Duty Washers GN 6339 → page QVX

How to order

GN 6343-NI-8-25-2

1	Material
2	Inner diameter d ₁
3	Outer diameter d ₂
4	Thickness s