



Metric table

1		2		3		Dimensions in: millimeters - <i>inches</i>									
d ₁	d ₂	Length l			d ₃	h ₁	h ₂								
45 <i>1.77</i>	M 8	20 <i>0.79</i>	30 <i>1.18</i>	-	21 <i>0.83</i>	26 <i>1.02</i>	10 <i>0.39</i>								
45 <i>1.77</i>	M 10	20 <i>0.79</i>	30 <i>1.18</i>	40 <i>1.57</i>	21 <i>0.83</i>	26 <i>1.02</i>	10 <i>0.39</i>								
56 <i>2.20</i>	M 8	20 <i>0.79</i>	30 <i>1.18</i>	40 <i>1.57</i>	26.5 <i>1.04</i>	29 <i>1.14</i>	11 <i>0.43</i>								
56 <i>2.20</i>	M 10	20 <i>0.79</i>	30 <i>1.18</i>	40 <i>1.57</i>	26.5 <i>1.04</i>	29 <i>1.14</i>	11 <i>0.43</i>								
56 <i>2.20</i>	M 12	30 <i>1.18</i>	40 <i>1.57</i>	50 <i>1.97</i>	26.5 <i>1.04</i>	29 <i>1.14</i>	11 <i>0.43</i>								
70 <i>2.76</i>	M 10	30 <i>1.18</i>	40 <i>1.57</i>	50 <i>1.97</i>	32.5 <i>1.28</i>	35 <i>1.38</i>	13 <i>0.51</i>								
70 <i>2.76</i>	M 12	30 <i>1.18</i>	40 <i>1.57</i>	50 <i>1.97</i>	32.5 <i>1.28</i>	35 <i>1.38</i>	13 <i>0.51</i>								