



Metric table

1 2

Dimensions in: millimeters / inches

b <sub>1</sub>	l <sub>1</sub> ±0.25	a	b <sub>2</sub>	d	h -1	l <sub>2</sub> ≈	l <sub>3</sub>	l <sub>4</sub> ≈	l <sub>5</sub> max.
26 1.02	350 13.78	17 0.67	14 0.55	M 8	69 2.72	526 20.71	328 12.91	18 0.71	9.5 0.37
26 1.02	450 17.72	17 0.67	14 0.55	M 8	69 2.72	632 24.88	428 16.85	18 0.71	9.5 0.37

3

**Specification**

**Arch handle**

- Aluminum
- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish

- SW
- SR

**End pieces**

- Zinc die-cast
- Powder coated
- Silver, RAL 9006, textured finish

**Set screws**

- Steel, zinc plated, blue passivated finish
- Property class 5.8

**Hex nuts ISO 4032-M8**

- Steel, zinc plated

**Washers DIN 125**

- Steel, zinc plated

RoHS

Arched pull handles GN 665 are produced from elliptical extrusions, and are notable for their elegant design.

see also...

	Page
GN 565.4 Arched Pull Handles (Aluminum, Mounting from the Back or Operator's Side)	QVX
GN 428 Cabinet U-Handles (Aluminum)	QVX

**Technical Information**

Strength Values of Screws	QVX
Load Capacity Information	QVX

How to order

1 2 3  
**GN 665-26-450-SW**

1	Handle width b <sub>1</sub>
2	Length l <sub>1</sub>
3	Finish

