



Metric



3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side (only for b₁ = 20 mm)

Metric table

Dimensions in: millimeters / inches

b ₁	l ₁	a	b ₂	d	h ₁	h ₂	h ₃	l ₂	l ₃	l ₄	r	t ₁ min.	t ₂
20 0.79	130 5.12	10 0.39	23 0.91	M 5	45 1.77	6.5 0.26	2.5 0.10	120 4.72	141 5.55	153 6.02	15 0.59	10 0.39	5 0.20
20 0.79	170 6.69	10 0.39	23 0.91	M 5	45 1.77	6.5 0.26	2.5 0.10	160 6.30	181 7.13	193 7.60	15 0.59	10 0.39	5 0.20
20 0.79	190 7.48	10 0.39	23 0.91	M 5	45 1.77	6.5 0.26	2.5 0.10	180 7.09	201 7.91	213 8.39	15 0.59	10 0.39	5 0.20
20 0.79	210 8.27	10 0.39	23 0.91	M 5	45 1.77	6.5 0.26	2.5 0.10	200 7.87	221 8.70	233 9.17	15 0.59	10 0.39	5 0.20
30 1.18	262 10.31	12 0.47	-	M 6	50 1.97	-	-	250 9.84	-	-	15 0.59	12 0.47	-
30 1.18	312 12.28	12 0.47	-	M 6	50 1.97	-	-	300 11.81	-	-	15 0.59	12 0.47	-
30 1.18	362 14.25	12 0.47	-	M 6	50 1.97	-	-	350 13.78	-	-	15 0.59	12 0.47	-
30 1.18	412 16.22	12 0.47	-	M 6	50 1.97	-	-	400 15.75	-	-	15 0.59	12 0.47	-

Specification

Handle

Aluminum

• Powder coated

- Black, RAL 9005, textured finish

- Silver, RAL 9006, textured finish

• Plain, tumbled finish

● **SW**

● **SR**

○ **BL**

Fastening set (Type B)

• Handle bases

Plastic, Polyamide (PA)

- Black, matte finish (for SW / BL)

- Light gray, matte finish (for SR)

• Socket cap screws DIN 7984

Steel, zinc plated, blue passivated finish

RoHS

On request

• Special lengths

• Various metric size fasteners and kit packaging

Cabinet U-handles GN 668 are manufactured from a bent aluminum profile. They can be mounted either from the back (type A) or by means of the handle base from the operator's side (type B).

see also...

GN 728 Economical Cabinet U-Handles

(Aluminum, Mounting from the Back or from the Operator's Side)

Page

QVX

Technical Information

Load Capacity Information

QVX

Plastic Characteristics

QVX

How to order

GN 668-20-130-A-SR

- 1** Handle width b₁
- 2** Length l₁
- 3** Type
- 4** Finish

