



**SS** Stainless Steel

**4 Type**

- MS** Brass tip
- KU** Plastic tip (Polyacetal POM)
- ZK** Spherical tip

**Metric table**

Dimensions in: millimeters - inches

| <b>1</b> d <sub>1</sub> | <b>2</b> d <sub>2</sub> | <b>3</b> l <sub>1</sub> |            |            |            | d <sub>3</sub> | d <sub>4</sub> | d <sub>5</sub> | d <sub>6</sub> +0.05 | h <sub>1</sub> | h <sub>2</sub> | l <sub>2</sub> | l <sub>3</sub> | l <sub>4</sub> ≈ |
|-------------------------|-------------------------|-------------------------|------------|------------|------------|----------------|----------------|----------------|----------------------|----------------|----------------|----------------|----------------|------------------|
| 34<br>1.34              | M 6                     | 15<br>0.59              | 20<br>0.79 | 25<br>0.98 | 30<br>1.18 | 16<br>0.63     | 4<br>0.16      | 3.5<br>0.14    | 4.5<br>0.18          | 21<br>0.83     | 10.5<br>0.41   | 1<br>0.04      | 1.3<br>0.05    | 5.1<br>0.20      |
| 42<br>1.65              | M 8                     | 20<br>0.79              | 25<br>0.98 | 30<br>1.18 | 40<br>1.57 | 19<br>0.75     | 6<br>0.24      | 5<br>0.20      | 6.1<br>0.24          | 26<br>1.02     | 13<br>0.51     | 1.5<br>0.06    | 1.6<br>0.06    | 6.2<br>0.24      |
| 53<br>2.09              | M 10                    | 25<br>0.98              | 30<br>1.18 | 40<br>1.57 | 50<br>1.97 | 24<br>0.94     | 8<br>0.31      | 6.5<br>0.26    | 7.8<br>0.31          | 32<br>1.26     | 16<br>0.63     | 2<br>0.08      | 1.9<br>0.07    | 7.3<br>0.29      |

**Specification**

- Knob body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black, matte finish
- Threaded stud  
Stainless steel AISI 304
- Cover cap  
Plastic  
Light gray, matte finish
- [Stainless Steel Characteristics](#) → page QVX
- [Plastic Characteristics](#) → page QVX
- [RoHS compliant](#)

**On request**

- Cover cap in other colors
- Printed lettering on cover cap

**Information**

GN 7336.5 hollow knurled knobs, type MS / KU with brass or plastic tip, are used when pressure dents or damage to the clamping surface must be avoided.

The ZK type features a spherical tip whose Ø d<sub>6</sub> is smaller than the core Ø of the thread. This version is suitable for holding GN 631 and GN 631.5 thrust pads, which need to be ordered separately.

These knobs have an attractive design with the advantage of a closed shape (no recess on the underside).

**see also...**

- [Thrust Pads GN 631 \(Technopolymer Plastic\)](#) → page QVX
- [Thrust Pads GN 631.5 \(Stainless Steel\)](#) → page QVX
- [Star Knobs GN 6336.10 \(with Brass / Plastic Tip\)](#) → page QVX
- [Star Knobs GN 6336.12 \(with Toggle Thrust Pad\)](#) → page QVX
- [Hollow Knurled Knobs GN 421.10 \(with Brass / Plastic Tip\)](#) → page QVX
- [Hollow Knurled Knobs GN 421.12 \(with Toggle Thrust Pad\)](#) → page QVX

**How to order**

**GN 7336.5-42-M8-25-MS**

|          |                                |
|----------|--------------------------------|
| <b>1</b> | Handle diameter d <sub>1</sub> |
| <b>2</b> | Thread d <sub>2</sub>          |
| <b>3</b> | Length l <sub>1</sub>          |
| <b>4</b> | Type                           |