



Metric table



Dimensions in: millimeters - *inches*

d ₁ Pipe thread	d ₂	l ₁	l ₂	s
G 1/4	20 <i>0.79</i>	9 <i>0.35</i>	3 <i>0.12</i>	6 <i>0.24</i>
G 3/8	22 <i>0.87</i>	9 <i>0.35</i>	4 <i>0.16</i>	8 <i>0.31</i>
G 1/2	28 <i>1.10</i>	11 <i>0.43</i>	4 <i>0.16</i>	10 <i>0.39</i>
G 3/4	32 <i>1.26</i>	12 <i>0.47</i>	4.5 <i>0.18</i>	12 <i>0.47</i>

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Black, matte finish
- Temperature resistant up to 212 °F (100 °C)
- Seal
Rubber NBR (Perbunan®)
- *Elastomer Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

- EN 746 threaded plugs are used to close bore holes with the listed pipe thread.
- see also...**
- *Threaded Plugs GN 749 (Steel)* → page QVX

<p>How to order</p> <p style="text-align: center;">EN 746-G3/8</p>	<p>1 Pipe thread d₁</p>
---	------------------------------------