



Metric



SS Stainless Steel

3 Type

- D** With tapped hole
- E** With threaded stud

Metric table

Dimensions in: millimeters / inches

1 d_1	2 d_2 Type D	2 d_3 Type E	d_4	h	Length l	t min.
16 0.63	M 5	M 6	10 0.39	18 0.71	10 0.39	7 0.28
20 0.79	M 6	M 8	12 0.47	24 0.94	12 0.47	9 0.35
25 0.98	M 6	M 8	14 0.55	29 1.14	14 0.55	9 0.35
32 1.26	M 8	M 10	18 0.71	37 1.46	16 0.63	12 0.47
36 1.42	M 10	M 12	20 0.79	42 1.65	18 0.71	15 0.59

Specification

GN 75

Steel

- Fine turned
- Blackend finish
- Zinc plated, blue passivated finish

ZB

GN75.5

Stainless steel AISI 304

- Matte shot-blasted finish
- Highly polished finish

**MT
PL**

RoHS

On request

- Stainless steel A4 quality

Mushroom shaped knobs GN 75 / GN 75.5 boast a compact and timeless design. Their non-scooping geometry combats dirt build-up and makes cleaning easier.

Mushroom shaped knobs GN 75 made of steel are mainly used in mechanical engineering. Mushroom shaped knobs GN 75.5 can be used in aggressive environments thanks to the stainless steel used.

see also...

	Page
GN 676.1 Push / Pull Knobs (Steel, Blackened Finish)	QVX
GN 676.2 Push / Pull Knobs (Steel, Zinc Plated)	QVX
GN 676.5 Push / Pull Knobs (Stainless Steel)	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order (Steel, blackened finish)

GN 75-25-M6-D

1 Handle diameter d_1
2 Thread d_2 (Threaded stud d_3)
3 Type

How to order (Steel, zinc plated)

GN 75-25-M8-E-ZB

1 Handle diameter d_1
2 Threaded stud d_3 (Thread d_2)
3 Type
4 Finish

How to order (Stainless steel)

GN 75.5-25-M8-E-MT

1 Handle diameter d_1
2 Threaded stud d_3 (Thread d_2)
3 Type
4 Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

