



Metric



3 Type

- D** With tapped hole
- E** With threaded stud

Metric table

1 d_1	2 d_2 Type D	2 d_3 Type E	d_4	h	Length l	t min.
17 0.67	M 5	M 5	10 0.39	14 0.55	9 0.35	7 0.28
21 0.83	M 6	M 6	12 0.47	17 0.67	10 0.39	11 0.43
25 0.98	M 6	M 6	14 0.55	21 0.83	10 0.39	11 0.43
33 1.30	M 8	M 8	18 0.71	29 1.14	14 0.55	12 0.47

Dimensions in: millimeters / inches

Specification

Knob

- Plastic, Phenolic (PF)
- Operating temperature up to 230 °F (110 °C)
- Black, shiny finish

Tapped insert (Type D)

Brass

Threaded stud (Type E)

Steel, zinc plated, blue passivated finish

RoHS

Mushroom shaped knobs GN 76 are widely used on push-pull type applications. The smooth shape gives the operator a comfortable grip.

see also...

	Page
EN 676 Knurled Knobs (Plastic, with Tapped Insert)	QVX
EN 676 Knurled Knobs (Plastic, with Threaded Stud)	QVX

Technical Information

Plastic Characteristics

Page

QVX

QVX

QVX

How to order

GN 76-25-M6-D

1	Handle diameter d_1
2	Thread d_2 (Threaded stud d_3)
3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

