



Metric table



Dimensions in: millimeters - inches

Size	d	l ₁	l ₂	m ₁	m ₂	s
220	6.5 0.26	48 1.89	36 1.42	32 1.26	20 0.79	6 0.24
440	8.5 0.33	65 2.56	54 2.13	45 1.77	30 1.18	8 0.31
850	10.5 0.41	75 2.95	75 2.95	55 2.17	55 2.17	10 0.39
1540	12.5 0.49	100 3.94	90 3.54	65 2.56	65 2.56	10 0.39

Specification

- Steel
- RoHS

Information

Base plates GN 810.19 are accessory for knee lever modules GN 810.12 / GN 810.13.

see also...

- *Knee Lever Modules GN 810.12 (with Horizontal or Vertical Mounting Base) → page QVX*
- *Knee Lever Modules GN 810.13 (with Weldable Base) → page QVX*
- *Handles GN 810.15 → page QVX*
- *Arm Levers GN 810.16 → page QVX*
- *Clamping Arm Extenders GN 810.17 → page QVX*
- *Bushings GN 810.18 → page QVX*

How to order

GN 810.19-220

1 Size

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

