



SS Stainless Steel

Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂	³ Length l			d ₃	b	h ₁	h ₂
1.81 46.0	1/4 x 20	0.625 15.9	0.750 19.1	1.000 25.4	0.51 13.0	0.24 6.1	0.89 22.6	0.24 6.1
1.81 46.0	5/16 x 18	0.625 15.9	0.750 19.1	1.000 25.4	0.51 13.0	0.24 6.1	0.89 22.6	0.24 6.1
2.28 57.9	5/16 x 18	0.750 19.1	1.000 25.4	1.250 31.8	0.63 16.0	0.28 7.1	1.04 26.4	0.28 7.1
2.28 57.9	3/8 x 16	0.750 19.1	1.000 25.4	1.250 31.8	0.63 16.0	0.28 7.1	1.04 26.4	0.28 7.1

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂	³ Length l			d ₃	b	h ₁	h ₂
46 1.81	M 6	16 0.63	20 0.79	25 0.98	13 0.51	6 0.24	22.5 0.89	6 0.24
46 1.81	M 8	16 0.63	20 0.79	25 0.98	13 0.51	6 0.24	22.5 0.89	6 0.24
58 2.28	M 8	20 0.79	25 0.98	30 1.18	16 0.63	7 0.28	26.5 1.04	7 0.28
58 2.28	M 10	20 0.79	25 0.98	30 1.18	16 0.63	7 0.28	26.5 1.04	7 0.28

Specification

- Stainless steel precision casting AISI CF-8
Matte shot-blasted finish **MT**
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Special inch or metric threaded stud sizes

Information

The ridges on the wings of GN 835 wing screws permit a better grip.

see also...

- Wing Screws GN 431 (Stainless Steel) → page 679
- Wing Screws GN 433 (Stainless Steel) → page 678
- Hand Knobs GN 6335.5 (Stainless Steel) → page 632

How to order	
¹	Handle diameter d ₁
²	Thread d ₂
³	Length l
⁴	Finish

GN 835-¹2.28-²3/8X16-³1.25-⁴MT

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4