



SS Stainless Steel

IF product design award

GERMAN DESIGN AWARD

Metric table

Dimensions in: millimeters - inches

| ¹ d ₁ | ² d ₂ | ³ Length l | | | | b | d ₃ | h ₁ | h ₂ ≈ |
|-----------------------------|-----------------------------|-----------------------|------------|------------|------------|------------|----------------|----------------|------------------|
| 32 1.26 | M 5 | 10 0.39 | 12 0.47 | 16 0.63 | 20 0.79 | 4 0.16 | 9 0.35 | 18 0.71 | 3 0.12 |
| 32 1.26 | M 6 | 12 0.47 | 16 0.63 | 20 0.79 | 25 0.98 | 4 0.16 | 9 0.35 | 18 0.71 | 3 0.12 |
| 40 1.57 | M 6 | 12 0.47 | 16 0.63 | 20 0.79 | 25 0.98 | 4 0.16 | 11 0.43 | 21 0.83 | 3 0.12 |
| 40 1.57 | M 8 | 16 0.63 | 20 0.79 | 25 0.98 | 30 1.18 | 4 0.16 | 11 0.43 | 21 0.83 | 3 0.12 |
| 50 1.97 | M 8 | 16 0.63 | 20 0.79 | 25 0.98 | 30 1.18 | 6 0.24 | 13 0.51 | 26 1.02 | 3 0.12 |
| 50 1.97 | M 10 | 20 0.79 | 25 0.98 | 30 1.18 | 40 1.57 | 6 0.24 | 13 0.51 | 26 1.02 | 3 0.12 |
| 63 2.48 | M 10 | 20 0.79 | 25 0.98 | 30 1.18 | 40 1.57 | 11 0.43 | 16 0.63 | 33 1.30 | 4 0.16 |
| 63 2.48 | M 12 | 25 0.98 | 30 1.18 | 40 1.57 | 50 1.97 | 11 0.43 | 16 0.63 | 33 1.30 | 4 0.16 |

Specification

Stainless steel precision casting AISI 316

- Matte shot-blasted finish

- Polished finish

⁴

MT

PL

• [Stainless Steel Characteristics](#) → page 2143

• [RoHS compliant](#)

Information

Wing screws GN 8350 clamp and fasten parts easily without tools. The ergonomic shape allows for high tightening forces.

The wing screws can also be used in particularly aggressive environments thanks to the material used.

see also...

- [Wing Nuts GN 8351 \(Stainless Steel, Hygienic Design\)](#) → page XYZ
- [Wing Nuts GN 8340 \(Stainless Steel\)](#) → page XYZ
- [Wing Screws GN 431 \(Stainless Steel\)](#) → page XYZ
- [Wing Screws GN 433 \(Stainless Steel\)](#) → page XYZ
- [Wing Screws GN 835 \(Stainless Steel\)](#) → page XYZ

How to order

¹ ² ³ ⁴
GN 8350-50-M10-30-MT

1 Handle diameter d₁

2 Thread d₂

3 Length l

4 Finish