



**Metric table**

Dimensions in: millimeters - inches

For pneumatic swing clamp size	<sup>2</sup> d <sub>1</sub> Thread	<sup>3</sup> m	d <sub>2</sub>	h	Length l
25	M 40 x 1.5	37 1.46	5.4 0.21	9 0.35	50 1.97
32	M 50 x 1.5	45 1.77	6.6 0.26	12 0.47	60 2.36
40	M 55 x 1.5	50 1.97	6.6 0.26	12 0.47	65 2.56
50	M 65 x 1.5	58 2.28	9 0.35	15 0.59	75 2.95
63	M 80 x 1.5	70 2.76	9 0.35	15 0.59	88 3.46

**Specification**

- Steel, zinc plated, blue passivated finish **ST**
- RoHS compliant

**Information**

GN 876.1 threaded flanges are accessories designed for GN 876 pneumatic swing clamps. This makes it unnecessary to tap the mounting hole of the part.

see also...

- *Pneumatic Swing Clamps GN 876 (Threaded Body Style)* → page 882
- *Slotted Spanner Nuts DIN 70852* → page 1135

How to order <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>GN876.1-ST-M55x1.5-50</b>	<b>1</b> Material
	<b>2</b> Thread d <sub>1</sub>
	<b>3</b> Hole distance m

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

