



SS Stainless Steel

Metric table



Dimensions in: millimeters - inches

d Thread	b	e	s
M 8 x 1	3.5 0.14	14.3 0.56	13 0.51
M 10 x 1	3.5 0.14	16.6 0.65	15 0.59
M 12 x 1.5	4 0.16	18.9 0.74	17 0.67
M 16 x 1.5	4.5 0.18	24.5 0.96	22 0.87
M 20 x 1.5	4.5 0.18	29.5 1.16	27 1.06

Specification



- Nut
 - Steel, blackened finish
 - Stainless steel AISI 303

BT
—

• *Stainless Steel Characteristics* → page 2143

• *RoHS compliant*

Information

GN 909 and GN 909.5 thin hex nuts expand the mounting options of indexing plungers and cam action indexing plungers.

How to order (Steel) GN909-M10x1-BT	1 Thread d
	2 Material
How to order (Stainless steel) GN909.5-M12x1.5	1 Thread d