



Inch table



Dimensions in: inches - millimeters

d ₁ Thread			d ₂	d ₃	h ₁	h ₂
10 x 24	10 x 32	1/4 x 20	0.75 19.1	0.50 12.7	0.22 5.6	0.16 4.1
5/16 x 18	3/8 x 16	-	0.75 19.1	0.50 12.7	0.31 7.9	0.25 6.4
1/2 x 13	5/8 x 11	-	1.00 25.4	0.75 19.1	0.38 9.7	0.25 6.4

Specification

- Low carbon steel, black oxide finish
- [RoHS compliant](#)

Information

CN check nuts may be used in combination with other components such as knurled head screws, torque thumb screws, hand knob assemblies, toggle shoe clamp assemblies and many other tooling applications.

see also...

- [Swivel Clamp Screws TS](#) → page 1128

How to order

CN-10X24

1 Thread d₁

