



Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂			d ₃	h ₁	h ₂	h ₃	t
1.25 31.8	10 x 24	10 x 32	1/4 x 20	0.63 16.0	1.31 33.3	0.50 12.7	0.81 20.6	0.38 9.7

Specification

- Wing body
Nylon plastic
 - Glass filled
 - Temperature resistant up to 230 °F (110 °C)
 - Black, matte finish
- Tapped insert
Brass, molded-in
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

- FKS wing nuts offer a taller profile to allow for simple two finger clamping.
- see also...**
- *Wing Nut FTK (Phenolic Plastic)* → page QVX

On request

- Additional thread sizes

How to order ¹ ² FKS-1.25-10X32	1 Handle diameter d ₁
	2 Thread d ₂