



**Inch table**

Dimensions in: inches - *millimeters*

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$	$d_3$	$h$	$t$
1.00 25.4	1/4 x 20	0.63 16.0	0.81 20.6	0.50 12.7
1.38 35.1	5/16 x 18	0.75 19.1	0.81 20.6	0.50 12.7
1.88 47.8	5/16 x 18	1.00 25.4	1.00 25.4	0.50 12.7
1.88 47.8	3/8 x 16	1.00 25.4	1.00 25.4	0.50 12.7

**Specification**

- Knurled nut  
Polypropylene plastic  
- Temperature resistant up to 150 °F (66 °C)  
- Black, matte finish
- Tapped insert  
Brass
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**On request**

- Additional thread sizes

**Information**

More shock proof than their phenolic counterpart, these KKBH knurled nuts provide excellent slip-free clamping and fastening.

How to order <sup>1</sup> <sup>2</sup> <b>KKBH-1.88-3/8X16</b>	<b>1</b> Handle diameter $d_1$
	<b>2</b> Thread $d_2$