



SS Stainless Steel

3 Type

- C With plain blind bore, tol. H7
- E With tapped blind bore
- D With tapped through bore

Inch table

1		2		3		Dimensions in: inches - millimeters		
d ₁	d ₂ Thread Type E / Type D		d ₃ +0.001 Bore Type C		d ₄	h	k	t min.
0.75 19.1	10 x 24	1/4 x 20	B 3/16	B 1/4	0.50 12.7	0.63 16.0	0.25 6.4	0.38 9.7
1.00 25.4	1/4 x 20	5/16 x 18	B 1/4	B 5/16	0.63 16.0	0.75 19.1	0.25 6.4	0.50 12.7
1.50 38.1	5/16 x 18	3/8 x 16	B 5/16	B 3/8	0.75 19.1	1.00 25.4	0.31 7.9	0.63 16.0
2.00 50.8	3/8 x 16	1/2 x 13	B 3/8	B 1/2	1.00 25.4	1.13 28.7	0.38 9.7	0.63 16.0
2.50 63.5	1/2 x 13	5/8 x 11	B 1/2	B 5/8	1.50 38.1	1.50 38.1	0.56 14.2	0.75 19.1
3.00 76.2	5/8 x 11	3/4 x 10	B 5/8	B 3/4	1.75 44.5	1.75 44.5	0.63 16.0	1.00 25.4

Specification

- Stainless steel AISI 303 **NI**
- Steel, blackened finish **ST**
- Machined from solid bar
- Knurled head for non-slip grip
- *Stainless Steel Characteristics* → page 2143
- RoHS compliant

Information

KRSK knurled nuts are used for applications which require higher durability than plastic or aluminum, yet appearance is essential.

see also...

- *Knurled Screws KRSK (with Threaded Stud)* → page 701

How to order	
1	Handle diameter d ₁
2	Bore d ₃ (Thread d ₂)
3	Type
4	Material

1 2 3 4
KRSK-1.00-B5/16-C-NI