



SS Stainless Steel

Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂	³ Length l		d ₃	h	k
0.75 19.1	10 x 24	0.50 12.7	1.00 25.4	0.50 12.7	0.63 16.0	0.25 6.4
0.75 19.1	1/4 x 20	0.75 19.1	1.25 31.8	0.50 12.7	0.63 16.0	0.25 6.4
1.00 25.4	1/4 x 20	1.75 44.5	-	0.63 16.0	0.75 19.1	0.25 6.4
1.00 25.4	5/16 x 18	1.75 44.5	3.00 76.2	0.63 16.0	0.75 19.1	0.25 6.4
1.50 38.1	5/16 x 18	1.75 44.5	3.00 76.2	0.75 19.1	1.00 25.4	0.31 7.9
1.50 38.1	3/8 x 16	1.75 44.5	3.00 76.2	0.75 19.1	1.00 25.4	0.31 7.9
2.00 50.8	3/8 x 16	1.75 44.5	3.00 76.2	1.00 25.4	1.13 28.7	0.38 9.7
2.00 50.8	1/2 x 13	1.75 44.5	-	1.00 25.4	1.13 28.7	0.38 9.7
2.50 63.5	1/2 x 13	1.75 44.5	3.00 76.2	1.50 38.1	1.50 38.1	0.56 14.2
2.50 63.5	5/8 x 11	1.75 44.5	-	1.50 38.1	1.50 38.1	0.56 14.2

Specification

- Stainless steel AISI 303 **NI**
- Steel, blackened finish **ST**
- Machined from solid bar
- Knurled head for non-slip grip
- Stud drilled and pinned into knurled knob body
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Special stud lengths and stud variations

Information

KRSK knurled screws are used for applications which require higher durability than plastic or aluminum, yet appearance is essential.

see also...

- *Knurled Nuts KRSK (with Tapped or Plain Bore)* → page 700

How to order	
¹	Handle diameter d ₁
²	Thread d ₂
³	Length l
⁴	Material

KRSK-1.50-5/16X18-3.00-NI

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4