



Inch table

Dimensions in: inches - *millimeters*

¹ l ₁	² s Square			l ₂	d ₂	h	l ₃	d ₁ Ø Handle
7.00 177.8	V 3/8	V 1/2	V 5/8	7.81 198.4	1.56 39.6	0.59 15.0	2.94 74.7	1.00 25.4
10.00 254.0	V 1/2	V 5/8	V 3/4	11.00 279.4	2.06 52.3	0.88 22.4	2.94 74.7	1.00 25.4
12.00 304.8	V 1/2	V 3/4	-	13.50 342.9	2.50 63.5	0.88 22.4	3.34 84.8	1.09 27.7

Specification

- Crank body
Steel
- Stamping
- Riveted
- Slim profile gears
- Reversing lever control in wrench head
- Opening
Through square
- Revolving handle DIN 98 → page 44
Steel, zinc plated, blue passivated finish
- Keyways WN / DIN 6885 → page XYZ / XYZ
- RoHS compliant

On request

- Other sizes, bore or hex openings
- Fixed or revolving handles
- With handles in steel or plastic

Information

The combination of crank and ratchet arm of these LR 318 ratcheting crank handles makes machinery adjustment faster, easier and safer.

Through hole design allows bolts or shafts to pass entirely through the ratcheting socket so, where required, nuts can then be secured at any part of the threaded length of the bolt or threaded shaft.

How to order ¹ ² LR318-7.00-V3/8	1 Length l ₁
	2 Square s

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4