



Metric



Metric table

Dimensions in: millimeters / inches

1 b	2 d	3 l ₁	h ₁	h ₂	l ₂	l ₃
21 0.83	M 6	93.5 3.68	36 1.42	30 1.18	112 4.41	15 0.59
26 1.02	M 6	117 4.61	41 1.61	34 1.34	139 5.47	15 0.59
27 1.06	M 6	132 5.20	45 1.77	37 1.46	156 6.14	15 0.59
28 1.10	M 6	179 7.05	50 1.97	42 1.65	204 8.03	15 0.59

Specification

Handle

- Nylon plastic
- Black, RAL 9005
- Operating temperature up to 230 °F (110 °C)

● SW,

Threaded studs

Steel, zinc plated

RoHS

On request

- Various metric size fasteners and kit packaging

The shape of cabinet U-handles MFP has good ergonomic features. Because of the style and durability of these handles, they are suitable for most industries.

see also...

MFB Cabinet U-Handles

Page

QVX

Technical Information

Strength Values

QVX

Plastic Characteristics

QVX

How to order

1 **2** **3** **4**
MFP-27-M6-132-SW

1 Handle width b

2 Thread d

3 Length l₁

4 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

